

MULTI-SHOOT SEEDING: VOS (Versatile Opener System)

3: CHOOSE YOUR FERTILIZER



684-HLD-2080***

FITS: CASE IH 800****
NEW HOLLAND P2070
FLEXI-COIL PD5700



694-HLD-2080

FITS: CASE IH ATX 700,
NEW HOLLAND P2060,
FLEXI-COIL PH5500 &
CONCORD EDGE ON
(84° SHANKS ONLY)




688-HLD-2080*****

FITS:
HORSCH 84° SHANK



610-TIP-4030
PAIRED ROW TIP




Overview: 4" (102 mm) Paired Row tip with extra long nose carbide and narrow carbide on the cutting edges of the wings. Two carbide inserts under the wings firm up the trench prior to seed placement.

Packer Recommendation:
4" (102 mm) or wider.

Fertilizer Options:
Used for seeding only.



610-TIP-4081
PAIRED ROW TIP



Overview: 4" (102 mm) Paired Row tip with horizontal and 3/4" (19 mm) vertical seed/fertilizer separation. Extra long nose carbide, narrow carbide on the cutting edges of the wings and under the wing to seal the fertilizer trench, and firm up the seed bed prior to seed placement.

Packer Recommendation: 4" (102 mm) or wider.

Fertilizer Options:

- G** Granular **L** Liquid **N** NH₃
- M** Pressurized NH₃ **N** **P** NH₃ + Phos

N **880-TUB-1001*******

Precision Drills NH₃
1/2" O.D. Stainless Tube

N **880-TUB-1002*******

C-Shank Drills NH₃
1/2" O.D. Stainless Tube

L **880-TUB-1003**

Precision Drills Liquid
1/4" O.D. Stainless Tube

L **880-TUB-1004**

C-Shank Drills Liquid
1/4" O.D. Stainless Tube

L **N** **880-TUB-1009**

Precision Drills Liquid or NH₃
3/8" O.D. Stainless Tube

L **N** **880-TUB-1010**

C-Shank Drills Liquid or NH₃
3/8" O.D. Stainless Tube

N **P** **880-TUB-1011**

Precision Drills Aqua NH₃ + Phos
1/4" O.D. Stainless Tube

N **P** **880-TUB-1012**

C-Shank Drills Aqua NH₃ + Phos
1/4" O.D. Stainless Tube

Notes:

* When installing on a 50° shank other than Bourgault or Ezee-On use wedge **880-WDG-0300** or **880-WSG-0301**. See page 106 for more information.

** Recommended for use with 3/4" single shoot tip **610-TIP-0802**.

*** Use bottom holes when mounting for use with **0802, 1711, 1712 & 3500** tips. To make this opener 3/4" deeper use top holes when installing the holder. See page 126-127 for more information.

**** Not recommended for use with Paired Row tip **610-TIP-4081**.

***** Use the bottom two holes when installing this holder for standard installation. To add 3° more pitch, use the top two holes on the holder.

***** For pressurized NH₃ order NH₃ tube and consult your pressurized system dealer for tubing inserts.

For a more detailed view of these components see page 126-127.